

Carbonyl Sulfide COS

Cylinder Pressure 2000 psig (138 bar)
 Cylinder Valve Outlet CGA No. 330
 DOT/TC Label Nonflammable
 Other Available Sizes SCOTTY™ Transportable

Recommended Equipment
 Two-Stage Regulator Model 215, Page 271
 Single-Stage Regulator Model 213, Page 271

| in Nitrogen | | | | Single-Certified Standards | |
|--------------------------|------|----------|----------------|----------------------------|---------------|
| | | | | Certified | |
| Concentration | Size | Contents | | Master Class | Working Class |
| | | CF | m ³ | | |
| ACULIFE 0.1 – 0.9 ppm | 30AL | 140 | 4 | | • |
| | 16AL | 74 | 2 | | • |
| | 7AL | 28 | 0.8 | | • |
| ACULIFE 1 – 9 ppm | 30AL | 140 | 4 | • | • |
| | 16AL | 74 | 2 | • | • |
| | 7AL | 28 | 0.8 | • | • |
| ACULIFE 10 – 49 ppm | 30AL | 140 | 4 | • | • |
| | 16AL | 74 | 2 | • | • |
| | 7AL | 28 | 0.8 | • | • |
| ACULIFE 50 – 999 ppm | 30AL | 140 | 4 | • | • |
| | 16AL | 74 | 2 | • | • |
| | 7AL | 28 | 0.8 | • | • |
| ACULIFE 0.1 – 3% | 44 | 209 | 6 | • | • |
| | 16 | 82 | 2 | • | • |
| | 7 | 32 | 0.9 | • | • |

Carbonyl sulfide calibration standards are also available in hydrocarbon balance gases. Contact your Air Liquide representative for more information.